

NEW AND USED MACHINES

LINE OF PRIMARY AND SECONDARY PACKAGING FOR POWDERS IN BOTTLES

PRODUCTION SPEED 2.000/2.500 BOTTLES/HOUR

AVAILABLE FORMATS



NEW ENTRY

MANY OTHER MACHINES CAN SEE AT OUR WAREHOUSE OR ON OUR WEBSITE:
www.pharmaworksmilano.com
VISIT US

MACHINES THAT COMPOSE THE LINE

1



2



3



4



5



6



7



8



9



10



11



12



13



14



15




MANY OTHER MACHINES CAN SEE AT OUR WAREHOUSE OR ON OUR WEBSITE:
www.pharmaworksmilano.com
VISIT US

LAYOUT OF INSTALLATION

PRIMARY PACKAGING

SECONDARY PACKAGING



LEGEND

- | | | |
|---------------------|--------------------|----------------------------|
| 1- ORIENTATOR | 6- CAPPING MACHINE | 11- CONNECTION |
| 2- CLEANING MACHINE | 7- CAPPING MACHINE | 12- LABELLING MACHINE |
| 3- DOSING MACHINE | 8- CONTROL | 13- CONTROL |
| 4- WEIGHING MACHINE | 9- SEALING MACHINE | 14- SLEEVE FITTING MACHINE |
| 5- METAL DETECTOR | 10- INK-JET | 15- OVEN-COLLECTION |

MANY OTHER MACHINES CAN SEE AT OUR WAREHOUSE OR ON OUR WEBSITE:
www.pharmaworksmilano.com
VISIT US